


Service Order

 <p>Steve De La Montanya 143 Meadow Place Windsor, CA 95492</p>	<p>11/12/2013 707-546-1070</p>	<p>EMS Redline Sprinter Type II "SE"</p> <p>720 Portal Street Cotati, CA 94931 Justin Calaway</p>	<p><i>Customer</i></p> <p>L 1264</p> <p><i>VIN Number</i></p> <p><i>Parent Job</i> 1264</p>
---	--------------------------------	--	--

Itemnumber Description

10 - BASE SECTION

10.

- | | | |
|-----|----|--|
| 10. | 1 | Prep van and misc |
| 10. | 33 | (2013 Mid Year) Sprinter "SE" Type II Base Conversion |
| 10. | 62 | (2013) Mercedes Benz Sprinter 2500 Van Chassis 144"
(Content of chassis and cost subject to change due to availability) |

STANDARD FEATURES

- 147 Arctic White Paint
- VH5 Lima Black Upholstery & Trim
- 3.0 Liter V6 Turbo Diesel Engine
- 188 hp @ 3,800 RPM
- 325 lb-ft of torque @ 1,400 - 2,400 rpm
- 5-Speed Automatic Transmission
- 220 Amp Alternator
- Front Stabilizer Bar
- Tire Pressure Monitoring System
- Shelf Above Windshield
- Adaptive Electronic Stability Program (ESP)
- Power Windows
- Remote Central Locking
- 4-Wheel Anti-Lock Braking System (ABS)
- Brake Assist (BAS)

OPTIONAL EQUIPMENT & PACKAGES

- High Roof
- (2) Additional Keys
- Daytime Running Lights
- Bracket For Aux A/C Compressor
- Alloy Wheels
- Seat Belt Orange, Driver and Passenger
- V01 Premium Package
- Window Package II
- RPM Governor Package
- Auxliary Battery With Disconnect

20 - PRE TAX

20.

- | | | |
|-----|---|--------------------------|
| 20. | 1 | Document Processing Fees |
|-----|---|--------------------------|



11/12/2013

Steve De La Montanya 707-546-1070
143 Meadow Place
Windsor, CA 95492

EMS Redline Sprinter Type II "SE"

Customer

L 1264

720 Portal Street
Cotati, CA 94931
Justin Calaway

707.975.3926

VIN Number

Parent Job 1264

Itemnumber Description

30.

40 - COMPLIANCE

40.

40. 1 Add KKK labels, attach to oxygen compartment and behind drivers seat.

51.

200 - INTERIOR CABINETS - STANDARD

A.

A. 1 Cabinet street side, rear, folding stretcher storage w/ 1" black strap & quick connect clip, removable lower shelf for access to cot fastener bolts & optional batteries.

A. 2 Cabinet street side, center, (2) storage cabinets w/ adjustable shelves, and sliding polycarbonate doors.

A. 3 Cabinet street side, "Action Wall", (1) upper storage cabinet w/ sliding polycarbonate doors, (1) lower storage cabinet w/ sliding polycarbonate doors, (1) lower hinged wood door w/ PVC banded edges w/ (2) vents & non-locking latch for Inverter access.

A. 4 Cabinet street side, forward, (2) storage cabinets w/ sliding polycarbonate doors, (1) open storage area to house (3) latex glove boxes.
NOTE: (3) boxes of latex gloves included.

A. 5 Cabinet street side upper, (2) storage cabinets w/ polycarbonate doors, (1) exhaust vent intake grille, (1) locking drug cabinet w/ hinged wood door w/ PVC banded edges w/ 7/8 keyed lock. A/C plenum located above storage cabinets w/ (5) air output rotating louvers.

A. 6 Street side solid partition with window opening & transverse oxygen cabinet below, w/ (1) oxygen access opening on cabinet face w/ hinged polycarbonate door w/ finger hole.

A. 7 Curb side partition & transverse oxygen cabinet below, oxygen cabinet will accept "H" or "M" tank, (1) oxygen access opening on cabinet face w/ hinged polycarbonate door, (1) hinged wood door with non-locking latch and PVC banded edges @ side for oxygen tank access w/ stainless steel protective sill. (2) ALS adjustable (powder coated) metal shelves 21"x12" w/ 1" upper lip (trim lock added to lip), fasten to aluminum uni-strut recessed into partition. Add a 1" aluminum lip (trim lock added to lip) bordering the outside edges to the top of the transverse oxygen cabinet below metal shelves. Supply (4) 1 inch black straps with quick connect clips, (1) per metal shelf & (2) on top of transverse oxygen cabinet.

A. 8 Upper partition cabinet w/ A/C platform, A/C evaporator housed inside. (A/C platform to have 110 & 12volt hole cut outs) Patient compartment face to have (1) storage cabinet w/ self closing hinged polycarbonate door w/ black pull ring latch, (LEADER "SE" engraved in polycarbonate) Cab side to have a hinged wood door w/ locking latch for access to electrical compartment, and (1) Gibraltar A/C intake vent.



11/12/2013

Steve De La Montanya 707-546-1070
143 Meadow Place
Windsor, CA 95492

EMS Redline Sprinter Type II "SE"

Customer

L 1264

720 Portal Street
Cotati, CA 94931
Justin Calaway

707.975.3926

VIN Number

Parent Job 1264

Itemnumber Description

A. 9 Squad Bench, curb side wall, slanted storage for oversized backboards, constructed of 16 gage aluminum. (2) hinged seat lids w/ gas cylinder hold open devices & rubber flex draw hold down latches per lid. (1) horizontal back rest and (1) horizontal head rest. Seat belt cut outs - (2) patient retractable lap belts, and (2) attendant retractable lap belts. Forward location for top drop (Kendall 5qt) sharps container & trash container, a single hinged red polycarbonate lid for trash container only w/ aluminum edge handle. NOTE: (1 Sharps and 1 Trash container included)

A. 10 Curb side, overhead cabinet above squad bench, (2) storage areas w/ sliding polycarbonate doors.

A. 11 Action wall panel, wood panel laminated with black formica with oxygen & electrical cut outs.

200 - INTERIOR CABINETS - OPTIONS

A. 200

A. 201 "SE" Center Console w/ (2) cup holders and map storage.

300 - INTERIOR TRIM AND COLOR - STANDARD

B.

B. 1 Floor color/material - (Non Coved) trimmed with aluminum cove molding along edges, Anti-Microbial, Lonseal - Lonfloor Flecks #500 Onyx.

B. 2 Headbumpers/Fillers upholstery color/material - Black Doeskin #DOS4849 w/ 1/4" closed cell foam.

B. 3 Seat Cushions / Back Rest / Head Rest, upholstery color/material - Black Doeskin #DOS4849 (seamless) w/ 2" foam for seat cushions & back rest, and 1 1/2" foam for head rest.

B. 4 Attendant seat, EVS #17803E Black high back (seamless) attendant seat w/ 3 point restraint, w/ Leader stamped into seat, w/ reinforced pedestal base #CBPED w/out track, seat is in a fixed location.

B. 5 Laminate color, exterior (upper) matte, Light Grey - D 355 / interior of cabinets to match exterior color.

B. 6 Laminate color, exterior (lower) matte, Dark Grey - 10592 / interior of cabinets to match exterior color. Stretcher cabinet to be laminated with Dakota Ridge.

B. 7 Headliner -- cab / patient compartment .- Cab to remain OEM, patient compartment to use 1/4" laminated masonite with White Matte finish.

B. 8 Polycarbonate color .240, Clear

B. 9 Polycarbonate sliding doors, retain handles on doors and provide holes for cable ties.

B. 10 Patient compartment door panels, OEM

B. 11 Insulation, foil backed bubble astro-cooler walls and roof areas.

300 - INTERIOR TRIM AND COLOR - OPTIONS



11/12/2013

Steve De La Montanya 707-546-1070
143 Meadow Place
Windsor, CA 95492

EMS Redline Sprinter Type II "SE"

Customer

L 1264

720 Portal Street
Cotati, CA 94931
Justin Calaway

707.975.3926

VIN Number

Parent Job 1264

Itemnumber Description

B. 300

B. 301 Rubber Mat Set (3), rubber mat inserts for (3) ALS shelf areas.

400 - WARNING DEVICES - STANDARD

C.

C. 1 Light bar front, Code III LED/HALOGEN, #LEDX2100/2158A, Red/Clear lense, steady Red in center section. (2) Cast Product aluminum mounting brackets.

C. 2 Warning lights rear, Code III 85A and 85R LED , (2) Red inboard, (2) Amber outboard. (lights only)

C. 3 Warning lights side, Code III 85R LED Red, (4) total.(2) per side (lights only).

C. 4 Warning lights grille, (2) Code III LED #TRX6R w/ chrome bezel, Red flashing, mounted on Leader style metal bracket located in upper corners of gille.

C. 5 Warning lights patient compartment, (2) Code III LED #TRX6R w/ chrome bezel, mounted in patient compartment on upper cabinet at rear, driver and passenger side. To activate w / PRI--SEC switch (both positions) and only when the rear patient compartment entry doors are open.

C. 6 Scene lights side , Code III # 41 Halogen w / 26 degree, (4) total. (2) per side (lights only).

C. 7 Scene lights rear, Code III # 41 Halogen 26 degree, mounted on interior headliner above rear doors.

C. 8 Clearance lights, Whelen LED (4) total. (2) front Amber, (2) rear Red, mounted in Cast Product light housing:

C. 9 Light housings aluminum, side, (4) total. (2) per side. Three light combo: Warning light 900 series / Scene light 700 series / Clearance light.

C. 10 Light housings, aluminum, rear, (2) driver--passenger , (2) light combo: Warning light 900 series / Warning light 900 series.

C. 11 Siren speaker, (2) 100 Watt CPI, driver and passenger sides, mounted through bumper.

C. 12 Back-up alarm, rear mounted, 97 decibel with auto reset, console defeat switch.

400 - WARNING DEVICES - OPTIONS

C. 400

C. 401 Intersection lights FRONT fenders, (2) 45BZR Code III LED (Red) flashing w/ chrome flange.

Note: K Spec

500 - ELECTRICAL CONTROL CENTER - STANDARD

D.

D. 1 Overhead console fiberglass, (201 Head Impact Compliant) w/ electrical components, circuit board.



11/12/2013

EMS Redline Sprinter Type II "SE"

Customer

L 1264

Steve De La Montanya 707-546-1070
143 Meadow Place
Windsor, CA 95492

720 Portal Street
Cotati, CA 94931
Justin Calaway

707.975.3926

VIN Number

Parent Job 1264

Itemnumber Description

- D. 2 Switch panel overhead, ("SE" Model w/ Black Finish) backlit, with cutouts, (12) legends included.
- D. 3 Siren electronic, w/ remote amp, mounted in overhead console, Whelen 295HFSA7 Ca. Spec. (high low deleted) flush mount bezel, dual tone, 100 watt output, w/ removable mic, hands free, horn ring control.
- D. 4 Indicator lamp Green, MASTER ON, C.H. LED pilot light.
- D. 5 Switch, PRI. SEC., center off, primary controls all emergency lights, secondary controls rear ambulance (outboard) warning lights only, panel mounted C.H. LED switch, lit Red/Amber.
- D. 6 Switch, BACK-UP ALARM, C.H., non-lit momentary.
- D. 7 Switch, LEFT FLOOD, C.H. LED, lit White.
- D. 8 Switch, RIGHT FLOOD, C.H. LED, lit White.
- D. 9 Switch, PATIENT DOME, 3-way, C.H. LED, lit Amber.
- D. 10 Switch, PATIENT HEAT/AC, 3-way, C.H. LED, lit Blue.
- D. 11 Switch, MODULE DISCONNECT, C.H. LED, lit Green.
- D. 12 Map light, Hella 19", mounted on OEM dash, passenger side.
- D. 13 Two-way radio power, Positive - Negative - Ignition, with terminal strip, located on partition wall behind drivers seat in cab.
NOTE: If optional center console is selected re-locate terminal strip to center console.

500 - ELECTRICAL CONTROL CENTER - OPTIONS

- D. 500
- D. 502 12 Volt wiring Positive-Negative pair, terminate behind drivers seat w/ 3 feet coil.

600 - ELECTRICAL PATIENT COMPARTMENT - STANDARD

- E.
- E. 1 Dome lamps, ceiling, (5) Flush mount Halogen High - Low, door jam switch and switch panel activated, door jam switch to activate all (5) in low intensity only, action wall switch activates all in high-low intensity.
- E. 2 Electrical outlet 12 volt, (2) , rear action wall, and ALS cabinet, cigarette style.
- E. 3 Electrical outlet (2) 120V, ALS cabinet, action wall, with pilot lights, mounted on grey plastic housings, wired to shore power.
- E. 4 Switch plate rear, (10) position Black Santex (switch plate only), back lit (includes legends)



11/12/2013

Steve De La Montanya 707-546-1070
143 Meadow Place
Windsor, CA 95492

EMS Redline Sprinter Type II "SE"

Customer

L 1264

720 Portal Street
Cotati, CA 94931
Justin Calaway

707.975.3926

VIN Number

Parent Job 1264

Itemnumber Description

- E. 5 Switch, DOME, 3-way, C.H. LED, lit Amber.
- E. 6 Switch, DOME HI-LO, C.H. (non lit)
- E. 7 Switch, EXHAUST, C.H. LED, lit Amber.
- E. 8 Switch, ELECT SUCTION, C.H. LED, lit Amber.
- E. 9 Switch, PATIENT HEAT A/C, 3-way, C.H. LED, lit Blue.
- E. 10 Switch, A/C, FAN HI-LO, C.H, (non-lit)
- E. 11 Switch, A/C, HEAT-COOL, C.H. lit Red - Blue
- E. 12 Shore power, 120V, 15 amp, behind driver door, Hubbell cast cover, wired to 110V outlets in patient compartment.
- E. 13 Restocking light timer, passenger rear filler, 5 minute, controls drivers side dome lights.
- E. 14 Step Well Light LED, located in side door step well, door switch activated. (Grote)
- E. 15 Inverter Pre-Wire, Includes 12 volt Pos-Neg with Anderson quick disconnect connector, terminating inside inverter compartment. (Does not include remote panel or rocker switch)

600 - ELECTRICAL PATIENT COMPARTMENT - OPTIONS

- E. 600
- E. 605 Battery Charger, IOTA 45 amp (connected to shoreline)
Note: K Spec

700 - ELECTRICAL AND MECHANICAL - STANDARD

- F.
- F. 1 Air conditioning / Heater, patient compartment, control air, additional compressor, auxiliary (3) fan condenser kit, mounted under vehicle driver side (mid - section). Patient system is independent of OEM cab system.
- F. 2 Power Exhaust vent, left rear, Cast Products exterior cover, interior louver round
- F. 3 Batteries (2) Total, OEM batteries to remain in original location.
- F. 4 Shut Down Timer, with 5 min. delay activated via ignition switch.
- F. 5 Wiring loom, Leader fabricated, hi temp SXL, color coded, number coded and function labeled, with split loom wire protection
- F. 6 Antenna wiring RG58AU (2), located in patient compartment ceiling behind two forward dome lights, terminates behind drivers seat in front cab.



11/12/2013

Steve De La Montanya 707-546-1070
143 Meadow Place
Windsor, CA 95492

EMS Redline Sprinter Type II "SE"

Customer

L 1264

720 Portal Street
Cotati, CA 94931
Justin Calaway

707.975.3926

VIN Number

Parent Job 1264

Itemnumber Description

F. 700

800 - OXYGEN SYSTEM - STANDARD

G.

G. 1 Aspirator, action wall area, SSCOR 22000, flush mount panel and gauge.

G. 2 Vacuum pump, 12V, w/vent tube to exterior.

G. 3 Oxygen system, (2) outlets Amico Ohio style quick release, mounted on grey plastic housings in action wall panel.

G. 4 Oxygen bottle rack, transverse mount, Leader Brand, Must Specify "M" or "H" tank.
(Leader Brand has the capability of stacking "M" size, one on top of the other)

800 - OXYGEN SYSTEM - OPTIONS

G. 800

G. 804 Oxygen regulator, preset 50 psi.

Note: K Spec

G. 820 Oxygen wrench, cable to wall by large bottle.

Note: K Spec

900 - HARDWARE -STANDARD

H.

H. 1 Seat belts, patient compartment, (4) sets of lap belts, (2) for squad bench attendants, (2) for squad bench patient.

H. 2 I.V. hardware, wall mount, (2), Chrome spring loaded clip type, surface mounted, (see print for location)

H. 3 (2) Pull handles, patient compartment interior rear doors.

H. 4 Ceiling grab rail, center mounted, stainless steel, 64 inch length, satin finish.

H. 5 Door sills (2) side & rear, bright stainless steel, with ramp edge at rear.

H. 6 Rear bumper step, (flip up) grip strut grating, grey powder coated.

H. 7 Hardware plates ceiling area, cargo net, grab bar, cabinetry

H. 8 Metal "C" shape safety strap for OEM door hold open, (passenger side only)



11/12/2013

EMS Redline Sprinter Type II "SE"

Customer

L 1264

Steve De La Montanya 707-546-1070
143 Meadow Place
Windsor, CA 95492

720 Portal Street
Cotati, CA 94931
Justin Calaway

707.975.3926

VIN Number

Parent Job 1264

Itemnumber Description

900 - HARDWARE - OPTIONS

H. 900

H. 901 Cargo Net, located @ head end of squad bench, Ancra fasteners, ratchet, 1 1/2" black webbing.

H. 905 Fire Extinguisher,ABC,5 Lb. Loose

Note: Quantity: Two (2)
K Spec

1000 -PATIENT HANDLING EQUIPMENT - STANDARD

I.

I. 1 Cot fastener, Stryker #6371, rear hook wall mount, front antlers removable. (specify cot model)

I. 1000

1100 -PAINT, BODY AND GRAPHICS - STANDARD

J.

J. 1 Emblems, Leader front fenders, rear doors, No Smoking labels, ETC.

1100 -PAINT, BODY AND GRAPHICS - OPTIONS

J. 1100

J. 1101 Add window tint to patient compartment OEM windows.

**NOTE: QUOTE IS GOOD FOR 60 DAYS FROM
DATE ON THIS DOCUMENT.**

Contract Total: \$74,055.00

FACTORY Representative

Date:

Sales Representative

Date:

[Empty box for Factory Representative signature]

[Empty box for Sales Representative signature]